



YSR8CFX14CLTCKITC

by Burndy
Catalog ID: YSR8CFX14CLTCKITC

Prop 65 Notice

Compression CU Reducer/Splice kit, W/InspWindow, Barrel A: #8 AWG (Flex-Str) Barrel B: #14 AWG (Str), Standard Barrel, Electro-Tin Plated

Product Details

General

| | |
|------------------------|----------------------|
| Color Code - Side A | Red |
| Connector Type | Reducer;Splice |
| Die Index - Element A | 49 |
| Die Index Run Side | 49 |
| Feature - Barrel Style | Skived |
| Feature - Barrel Type | Standard |
| Material | Copper |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Temperature Rating | 194 |
| Trade Name | HYREDUCER™ |
| UPC | 781810473986 |
| UPC 12 Digit | 7818104739866 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - B Length fraction | 9/16 in |
| Dimension - B Length inch | 0.57 in |
| Dimension - L Length Overall mm | 36 mm |
| Dimension - Length BB inch | 0.66 in |
| Dimension - Length Overall inch | 1.41 in |
| Dimension - Strip Length inch | 0.57 in |

Electrical Ratings

| | |
|--------------------------|-------|
| Rating - KVA | 35 kV |
| Rating - Minimum Voltage | 600 |
| Voltage - Maximum | 35000 |

Conductor Related

| | |
|--|--------|
| Conductor - Copper Flex G Size A | 8 AWG |
| Conductor - Copper Flex G Size A Range | 8 AWG |
| Conductor - Copper Flex G Size B | 10 AWG |

| | |
|--|----------|
| Conductor - Copper Flex G Size B Range | 10 AWG |
| Conductor - Copper Flex H Size A | 8 AWG |
| Conductor - Copper Flex H Size A Range | 8 AWG |
| Conductor - Copper Flex H Size B | 10 AWG |
| Conductor - Copper Flex H Size B Range | 10 AWG |
| Conductor - Copper Flex I Size A | 8 AWG |
| Conductor - Copper Flex I Size A Range | 8 AWG |
| Conductor - Copper Flex I Size B | 10 AWG |
| Conductor - Copper Flex I Size B Range | 10 AWG |
| Conductor - Copper Flex K Size A | 8 AWG |
| Conductor - Copper Flex K Size A Range | 8 AWG |
| Conductor - Copper Flex K Size B | 10 AWG |
| Conductor - Copper Flex K Size B Range | 10 AWG |
| Conductor - Copper Flex M Size A | 8 AWG |
| Conductor - Copper Flex M Size A Range | 8 AWG |
| Conductor - Copper Flex M Size B | 10 AWG |
| Conductor - Copper Flex M Size B Range | 10 AWG |
| Conductor - Copper Solid Size A | 6 |
| Conductor - Copper Solid Size B | 12;11;10 |
| Conductor - Copper Str Size B | 10 AWG |

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)