

YST1C1CT

by Burndy
Catalog ID: YST1C1CT

Prop 65 Notice

UNINSULATED HIGH VOLTAGE COPPER COMPRESSION SPLICE
STANDARD BARREL-TAPERED ENDS.



Product Details

General

Color Code - Side A	Green
Color Code - Side B	Green
Connector Type	Tap
Die Index Run Side	11
Die Index Tap Side	11
Feature - Barrel Style	Tapered
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYTEE™
UPC	781810198490
UPC 12 Digit	7818101984900

Dimensions

Dimension - B Length fraction	1-3/8 in
Dimension - B Length inch	1.38 in
Dimension - Inside Diameter inch	0.36 in
Dimension - L Length Overall mm	95 mm
Dimension - Length BB inch	1.38 in
Dimension - Length Overall inch	3.75 in
Dimension - Outside Diameter inch	0.46 in
Dimension - Width inch	1.61 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Run	1 AWG
----------------------------	-------

Conductor - Copper Str Run Range	1 AWG
Conductor - Copper Str Tap	1 AWG
Conductor - Copper Str Tap Range	1 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)