

YSU25R2R

by Burndy
Catalog ID: YSU25R2R

Prop 65 Notice

Heavy-walled AL tubing with solid barrier minimizes galvanic corrosion,
Color Code: Yellow (Side A), Red (Side B)



Product Details

General

Color Code - Side A	Yellow
Color Code - Side B	Red
Die Index	243;BG or 5/8
Material	Aluminum
Plated	Y
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	LINKIT™
Type	Service Entrance, Uninsulated, Center Stop
UPC	781810143285
UPC 12 Digit	7818101432855

Dimensions

Dimension - B Length inch	0.87 in
Dimension - L Length Overall mm	51 mm
Dimension - Length Overall inch	2 in
Dimension - Outside Diameter inch	0.65 in

Conductor Related

Conductor - ACSR Str Size A	1/0 (6/1) Raven AWG
Conductor - ACSR Str Size B	2 (6/1) Sparrow AWG;2 (7/1) Sparate AWG
Conductor - ACSR Str Size B Range	2 (6/1) Sparrow AWG-2 (7/1) Sparate AWG
Conductor - AL Str Size A	1/0 AWG
Conductor - AL Str Size B	2 AWG;1 AWG
Conductor - AL Str Size B Range	2 AWG-1 AWG
Conductor - Copper Str Size A	1/0 AWG
Conductor - Copper Str Size B	1 AWG, 2 AWG, 3 AWG
Conductor - Copper Str Size B Range	1 AWG- 3 AWG

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)