

YSU2R2R

by Burndy
Catalog ID: YSU2R2R

Prop 65 Notice

Heavy-walled AL tubing with solid barrier minimizes galvanic corrosion, Color Code:Red (Side A&B).

Features: Heavy-Walled Aluminum Tubing With Solid Barrier Minimizes Galvanic Corrosion Of Conductors, Accommodates Neutral Strands Of Type SE Service Entrance Conductor As Well As Other Conductors, Installed With Standard Tooling, Color Coded, Pre-Filled With PENE TROX Joint Compound And Stripsealed, Die Index: BG Element A, Conductor Type: Side A And Side B: ACSR, Aluminum, Copper, Tools, Die Set Catalog Number, And (number Of Crimps): HYTOOL: OH25 Tool, (1), MD6, MD7 Tool, (3), MD6, MD7 Tool, W-BG Die, (1), OUR840 Tool, X-NBG Die, (1), HYPRESS: Y35 Tool, U-BG Die, (1), Y35L, Y750 Tool, Color Code: Red (Side A And B)



Product Details

General

| | |
|---------------------------|--|
| Application | For Combinations Of Copper, Aluminum, ACSR, 6201, 5005 and Compressed Conductors |
| Color Code - Side A | Red |
| Color Code - Side B | Orange |
| Die Index | 243;BG or 5/8 |
| Material | Aluminum |
| Plated | Y |
| Plating Type | Unplated |
| Prefilled Oxide Inhibitor | Y |
| Sub Brand | LINKIT |
| Trade Name | LINKIT™ |
| Type | Service Entrance, Uninsulated, Center Stop |
| UPC | 781810141083 |
| UPC 12 Digit | 7818101410833 |

Dimensions

| | |
|-----------------------------------|---------|
| Dimension - B Length inch | 0.87 in |
| Dimension - L Length Overall mm | 51 mm |
| Dimension - Length Overall inch | 2 in |
| Dimension - Outside Diameter inch | 0.65 in |

Conductor Related

| | |
|-----------------------------------|------------------------|
| Conductor - ACSR Str Size A | 2(6/1) AWG,2 (7/1) AWG |
| Conductor - ACSR Str Size A Range | 2(6/1) AWG-2(7/1) AWG |
| Conductor - ACSR Str Size B | 4(6/1) AWG,4 (7/1) AWG |
| Conductor - ACSR Str Size B Range | 4(6/1) AWG-4 (7/1) AWG |
| Conductor - AL Str Size A | 2 AWG;1 AWG |

| | |
|-------------------------------------|---------------------|
| Conductor - AL Str Size A Range | 2 AWG-1 AWG |
| Conductor - AL Str Size B | 3 AWG, 4 AWG |
| Conductor - AL Str Size B Range | 3 AWG- 4 AWG |
| Conductor - Copper Solid Size B | 2 AWG |
| Conductor - Copper Str Size A | 1 AWG, 2 AWG, 3 Awg |
| Conductor - Copper Str Size A Range | 1 AWG-3 AWG |
| Conductor - Copper Str Size B | 3 AWG, 4 AWG |
| Conductor - Copper Str Size B Range | 3 AWG- 4 AWG |

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|-----|
| Minimum Pack Quantity | 100 |
|-----------------------|-----|

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)