

YSU2W2W

by Burndy
Catalog ID: YSU2W2W

Prop 65 Notice

Heavy-walled AL tubing with solid barrier minimizes galvanic corrosion, Color Code:Orange (Side A), Orange (Color Code).

Features: Heavy-Walled Aluminum Tubing With Solid Barrier Minimizes Galvanic Corrosion Of Conductors, Accommodates Neutral Strands Of Type SE Service Entrance Conductor As Well As Other Conductors, Installed With Standard Tooling, Color Coded, Pre-Filled With PENE TROX Joint Compound And Stripsealed, Conductor Type: Side A And Side B: ACSR, Aluminum, Copper, Die Index: BG Element A, Color Code: Orange (Side A And B), Tools, Die Set Catalog Number, And (number Of Crimps): HYTOOL: OH25 Tool, (1), MD6, MD7 Tool, (3), MD6, MD7 Tool, W-BG Die, (1), OUR840 Tool, X-NBG Die, (1), HYPRESS: Y35 Tool, U-BG Die, (1), Y35L, Y750 Tool



Product Details

General

Application	For Combinations Of Copper, Aluminum, ACSR, 6201, 5005 and Compressed Conductors
Color Code - Side A	Orange
Color Code - Side B	Orange
Die Index	243;BG or 5/8
Material	Aluminum
Plated	Y
Plating Type	Tin - Hot Dipped
Prefilled Oxide Inhibitor	Y
Sub Brand	LINKIT
Trade Name	LINKIT™
Type	Service Entrance, Uninsulated, Center Stop
UPC	781810141946
UPC 12 Digit	7818101419466

Dimensions

Dimension - B Length inch	0.87 in
Dimension - L Length Overall mm	51 mm
Dimension - Length Overall inch	2 in
Dimension - Outside Diameter inch	0.65 in

Conductor Related

Conductor - ACSR Str Size A	4 (6/1) Swan AWG;4 (7/1) Swanate AWG
Conductor - ACSR Str Size A Range	4 (6/1) Swan AWG-4 (7/1) Swanate AWG
Conductor - ACSR Str Size B	4 (6/1) Swan AWG;4 (7/1) Swanate AWG
Conductor - ACSR Str Size B Range	4 (6/1) Swan AWG-4 (7/1) Swanate AWG
Conductor - AL Str Size A	3 AWG, 4 AWG

Conductor - AL Str Size A Range	3 AWG- 4 AWG
Conductor - AL Str Size B	3 AWG, 4 AWG
Conductor - AL Str Size B Range	3 AWG- 4 AWG
Conductor - Copper Solid Size A	2 AWG
Conductor - Copper Solid Size B	2 AWG
Conductor - Copper Str Size A	3 AWG, 4 AWG
Conductor - Copper Str Size A Range	3 AWG-4 AWG
Conductor - Copper Str Size B	3 AWG, 4 AWG
Conductor - Copper Str Size B Range	3 AWG-4 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)