

YSU2W4W

by Burndy
Catalog ID: YSU2W4W

Prop 65 Notice

Heavy-walled AL tubing with solid barrier minimizes galvanic corrosion,
Color Code:Orange (Side A), Blue (Color Code)



Product Details

General

Color Code - Side A	Orange
Color Code - Side B	Blue
Die Index	243;BG or 5/8
Material	Aluminum
Plated	Y
Plating Type	Tin - Hot Dipped
Prefilled Oxide Inhibitor	Y
Trade Name	LINKIT™
Type	Service Entrance, Uninsulated, Center Stop
UPC	781810142080
UPC 12 Digit	7818101420800

Dimensions

Dimension - B Length inch	0.87 in
Dimension - L Length Overall mm	51 mm
Dimension - Length Overall inch	2 in
Dimension - Outside Diameter inch	0.65 in

Conductor Related

Conductor - ACSR Str Size A	4 (6/1) Swan AWG;4 (7/1) Swanate AWG
Conductor - ACSR Str Size A Range	4 (6/1) Swan AWG-4 (7/1) Swanate AWG
Conductor - ACSR Str Size B	6 (6/1) Turkey AWG
Conductor - AL Str Size A	3 AWG, 4 AWG
Conductor - AL Str Size A Range	3 AWG- 4 AWG
Conductor - AL Str Size B	5 AWG, 6 AWG
Conductor - AL Str Size B Range	5 AWG-6 AWG
Conductor - Copper Solid Size A	2 AWG
Conductor - Copper Solid Size B	4 AWG
Conductor - Copper Str Size A	3 AWG, 4 AWG
Conductor - Copper Str Size A Range	3 AWG-4 AWG
Conductor - Copper Str Size B	5 AWG, 6 AWG

Conductor - Copper Str Size B Range	5 AWG-6 AWG
-------------------------------------	-------------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)