



YSV10BBOX

by Burndy
Catalog ID: YSV10BBOX

Butt Splices, 12 AWG-10 AWG, .75 in L, Connector Type Bare Butted Seam.

Features: HYLINK Type YSV Seamless Splice Connector Is Used To Splice Stranded And Solid Copper Conductors In Virtually All Heavy Duty Industrial And General Purpose Applications, Manufactured From Seamless Tubing: A High Quality Design With No Seams To Split, Electrolytic Copper: Provides Maximum Conductivity, Low Resistance And Ductility For Excellent Crimp Forming Properties, Electro-Tin Plated: Provides Durable Long Lasting Resistance To Corrosion, Positive Center Wire Stops: Provides Proper Depth Of Wire Insertion, Marked With Wire Size: Provides Easy Wire Size Identification, The HYLINK Splice Connectors Have Inspection Holes: Provides Easy Visual Inspection For Proper Wire Insertion, Conductor Type: Solid, Installation Tool: HYTOOL: Non-Ratchet: Y10D, Y10-22 Tool, Ratchet: Y8MRB-1, MR20, MR8G98, MR8-9Q Tool, Insulation Support: No, Package: Box, Wire Strip Length: 5/16 IN

Product Details

General

Application	For All Heavy Duty Industrial And General Purpose Applications
Connector Type	Splice
Feature - Barrel Style	Chamfered
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	Splice
UPC	781810525524

Dimensions

Dimension - L Length Overall mm	19 mm
Dimension - Length Overall inch	0.75 in
Dimension - Strip Length inch	5/16 in

Electrical Ratings

Voltage - Maximum	35000 V
-------------------	---------

Conductor Related

Conductor - Copper Solid Size	12-10 AWG
Conductor - Copper Str Size	12-10 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Solid-Size • CU C Str Aircraft-Size

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100 EA
Minimum Pack Quantity	50

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)