



# YSV10NK

by Burndy  
Catalog ID: YSV10NK

Prop 65 Notice

UNINSULATED BUTT SPLICE, 600 VOLTS MAXIMUM.

## Product Details

### General

Connector Type	Splice
Die Index	36
Feature - Barrel Style	Chamfered
Material	Copper
Plated	Y
Plating Type	Nickel
Trade Name	HYLINK™
Type	Splice
UPC	781810162781
UPC 12 Digit	7818101627811

### Dimensions

Dimension - B Length fraction	5/16 in
Dimension - B Length inch	0.31 in
Dimension - Inside Diameter inch	0.13 in
Dimension - L Length Overall mm	19 mm
Dimension - Length Overall inch	0.75 in
Dimension - Outside Diameter inch	0.21 in
Dimension - Strip Length inch	5/16

### Electrical Ratings

Voltage - Maximum	35000 V
-------------------	---------

### Conductor Related

Conductor - Copper Solid Size	12;11;10
Conductor - Copper Solid Size Range	12-10
Conductor - Copper Str Aircraft Size	AN 12;AN 10
Conductor - Copper Str Aircraft Size Range	AN 12-AN 10
Conductor - Copper Str Navy Size	6 (7);6 (19);9 (7);9 (37)
Conductor - Copper Str Navy Size Range	6 (7)-9 (37)
Conductor - Copper Str Size	12;10
Conductor - Copper Str Size Range	12-10

Conductor Type	<ul style="list-style-type: none"><li>• CU C Str-Size</li><li>• CU C Solid-Size</li><li>• CU C Str Aircraft-Size</li></ul>
----------------	--

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1000
-----------------------	------

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)