



YSV18BBOX

by Burndy
Catalog ID: YSV18BBOX

Butt Splices, 22 AWG-18 AWG, .62 in L, Connector Type Bare Butted Seam.

Features: HYLINK Type YSV Seamless Splice Connector Is Used To Splice Stranded And Solid Copper Conductors In Virtually All Heavy Duty Industrial And General Purpose Applications, Manufactured From Seamless Tubing: A High Quality Design With No Seams To Split, Electrolytic Copper: Provides Maximum Conductivity, Low Resistance And Ductility For Excellent Crimp Forming Properties, Electro-Tin Plated: Provides Durable Long Lasting Resistance To Corrosion, Positive Center Wire Stops: Provides Proper Depth Of Wire Insertion, Marked With Wire Size: Provides Easy Wire Size Identification, The HYLINK Splice Connectors Have Inspection Holes: Provides Easy Visual Inspection For Proper Wire Insertion, Package: Box, Insulation Support: No, Installation Tool: HYTOOL: Non-Ratchet: Y10D, Y10-22 Tool, Ratchet: Y8MRB-1, MR20, MR8G98, MR8-9Q Tool, Conductor Type: Solid, Wire Strip Length: 1/4 IN

Product Details

General

Application	For All Heavy Duty Industrial And General Purpose Applications
Connector Type	Splice
Feature - Barrel Style	Chamfered
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	Splice
UPC	781810525548

Dimensions

Dimension - L Length Overall mm	16 mm
Dimension - Length Overall inch	0.62 in
Dimension - Strip Length inch	1/4

Electrical Ratings

Voltage - Maximum	35000 V
-------------------	---------

Conductor Related

Conductor - Copper Solid Size	22-18 AWG
Conductor - Copper Str Size	22-18 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Solid-Size • CU C Str Aircraft-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)