



YSV18SV

by Burndy
Catalog ID: YSV18SV

UNINSULATED BUTT SPLICE, 600 VOLTS MAXIMUM.

Product Details

General

Connector Type	Splice
Die Index	36
Feature - Barrel Style	Chamfered
Material	Copper
Plated	Y
Plating Type	Silver
Type	Splice
UPC 12 Digit	0

Dimensions

Dimension - B Length fraction	1/4 in
Dimension - B Length inch	0.25 in
Dimension - Inside Diameter inch	0.06 in
Dimension - L Length Overall mm	16 mm
Dimension - Length Overall inch	0.62 in
Dimension - Outside Diameter inch	0.12 in
Dimension - Strip Length inch	1/4

Electrical Ratings

Voltage - Maximum	35000 V
-------------------	---------

Conductor Related

Conductor - Copper Solid Size	20;18
Conductor - Copper Solid Size Range	20-18
Conductor - Copper Str Aircraft Size	AN 22;AN 20;AN 18
Conductor - Copper Str Aircraft Size Range	AN 22-AN 18
Conductor - Copper Str Navy Size	1 (1);1 (7);1 (10);1 1/2 (1);1 1/2 (7);1 1/2 (16);1 1/2 (41);2 (7);2 1/2 (1);2 1/2 (19);2 1/2 (26)
Conductor - Copper Str Navy Size Range	1 (1)-2 1/2 (26)
Conductor - Copper Str Size	22;20;18
Conductor - Copper Str Size Range	22-18

Conductor Type	<ul style="list-style-type: none">• CU C Str-Size• CU C Solid-Size• CU C Str Aircraft-Size
----------------	--

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1000
-----------------------	------

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)