

# YSV1CFXB

by Burndy  
Catalog ID: YSV1CFXB

Cu Compression Belled End Splice, #1 STR AWG, 600 V to 35 KV, Long Barrel, Green, 11 Index



## Product Details

### General

Color Code	Green
Connector Type	Splice
Die Index	11
Feature - Barrel Style	Belled
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLINK™
Type	Splice
UPC	781810099902

### Dimensions

Dimension - B Length fraction	1-1/2 in
Dimension - B Length inch	1.50 in
Dimension - D inch	0.60 in
Dimension - L Length Overall mm	81 mm
Dimension - Length Overall inch	3.18 in
Dimension - Outside Diameter inch	0.51 in
Dimension - Strip Length inch	1-9/16 in

### Conductor Related

Conductor - Copper DLO Size	1 (225/#24) DLO
Conductor - Copper Flex G Size	1 AWG
Conductor - Copper Flex H Size	1 AWG
Conductor - Copper Flex I Size	1 AWG
Conductor - Copper Flex K Size	1 AWG
Conductor - Copper Flex M Size	1 AWG
Conductor - Copper Solid Size	1 AWG
Conductor - Copper Str Compact Size	1
Conductor - Copper Str Compact Size Range	1

Conductor - Copper Str Navy Size	75 (37)
Conductor - Copper Str Size	1 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	10
-----------------------	----

### For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)