

YSV25FXB

by Burndy
Catalog ID: YSV25FXB

Prop 65 Notice

Compression Splice, 1/0 AWG, 600 - 35000 V, 3.18 IN L, Die Index: 12.

Features: Long Barrel Length: High Voltage Terminations, Four (4) Center Conductor Stops: Provides A Center Wire Stop For Proper Conductor Insertion, High Pull Out Force: Provides Added Security For Greater Mechanical And Electrical Properties, Belled Cable Entry: A Funnel Type Entry Provide Easy Insertion Of Extra Flexible Cables Plus Offers Mechanical Strain Relief For Individual Strands, Color Code: Pink, Dieless Tools (number Of Crimps): Y81KFT, Y81KFTMBH, PAT81KFT-18V Tool, (1), Oil Stop: No, Tapered End: No, Die Index: 12 Element A, Conductor Type: Flexible Copper, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y39, Y750 Tool, U25RT Die, (4), Y46 Tool, U25RT Die With PUADP-1 Adapter, (4), Wire Strip Length: 1-9/16 IN



Product Details

General

Application	For Higher voltage applications
Color Code	Pink
Connector Type	Splice
Die Index	12
Feature - Barrel Style	Belled
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	Splice
UPC	781810041451

Dimensions

Dimension - B Length fraction	1-1/2 in
Dimension - B Length inch	1.50 in
Dimension - D inch	0.66 in
Dimension - L Length Overall mm	81 mm
Dimension - Length Overall inch	3.18 in
Dimension - Outside Diameter inch	0.56 in
Dimension - Strip Length inch	1-9/16 in

Conductor Related

Conductor - Copper DLO Size	1/0 (275/#24) DLO
Conductor - Copper Flex G Size	1/0 AWG
Conductor - Copper Flex H Size	1/0 AWG

Conductor - Copper Flex I Size	1/0 AWG
Conductor - Copper Flex K Size	1/0 AWG
Conductor - Copper Flex M Size	1/0 AWG
Conductor - Copper Solid Size	1/0 AWG
Conductor - Copper Str Compact Size	1/0
Conductor - Copper Str Compact Size Range	1/0
Conductor - Copper Str Navy Size	100 (61)
Conductor - Copper Str Size	1/0 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)