

## YSV27FXB

by Burndy  
Catalog ID: YSV27FXB

Prop 65 Notice

Copper Compression Splice, 3/0 Flex, 3.46" Splice Length, Long Barrel, Belled End, Tin Plated



## Product Details

### General

Color Code	Orange
Connector Type	Splice
Die Index	14
Feature - Barrel Style	Belled
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin
Trade Name	HYLINK™
Type	Splice
UPC	781810041475

### Dimensions

Dimension - B Length fraction	1-5/8 in
Dimension - B Length inch	1.64 in
Dimension - D inch	0.82 in
Dimension - L Length Overall mm	88 mm
Dimension - Length Overall inch	3.46 in
Dimension - Outside Diameter inch	0.70 in
Dimension - Strip Length inch	1-11/16 in

### Conductor Related

Conductor - Copper DLO Size	3/0 (450/#24) DLO
Conductor - Copper Flex G Size	3/0 AWG
Conductor - Copper Flex H Size	3/0 AWG
Conductor - Copper Flex I Size	3/0 AWG
Conductor - Copper Flex K Size	3/0 AWG
Conductor - Copper Flex M Size	3/0 AWG
Conductor - Copper Solid Size	3/0 AWG
Conductor - Copper Str Compact Size	3/0
Conductor - Copper Str Compact Size Range	3/0

Conductor - Copper Str Navy Size	150 (61)
Conductor - Copper Str Size	3/0 AWG
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul>

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	100
-----------------------	-----

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)