



YSV28LBOX

by Burndy
Catalog ID: YSV28LBOX

Prop 65 Notice

Copper Hylink, 4/0, 1.94 in L, Uninsulated Butt Splice 600 Volts Maximum.

Features: Uninsulated butt splice, Manufactured from seamless tubing, Electro-tin plated

Product Details

General

Application	UNINSULATED BUTT SPLICE
Connector Type	Splice
Die Index	46
Feature - Barrel Style	Chamfered
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	SPLICE, HYLINK
Trade Name	HYLINK™
Type	Splice
UPC	781810324714

Dimensions

Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.88 in
Dimension - L Length Overall mm	49 mm
Dimension - Length Overall inch	1.94 in
Dimension - Outside Diameter inch	0.77 in
Dimension - Strip Length inch	7/8 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Solid Size	4/0 AWG
Conductor - Copper Str Aircraft Size	AN 0000
Conductor - Copper Str Size	4/0 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Solid-Size • CU C Str Aircraft-Size

Certifications and Compliance

Certification - CSA Approved	Yes
------------------------------	-----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)