



## YSV2CLBOX

by Burndy  
Catalog ID: YSV2CLBOX

Prop 65 Notice

Copper Hylink, 21.41 in L, Uninsulated Butt Splice 600 Volts Maximum.

Features: HYLINK Type YSV-L Seamless Splice Connector Is Used To Splice Type AN Aircraft Cables Plus Commercial Stranded And Solid AWG Conductors, Suitable For Aircraft, Light Duty Industrial And General Purpose Applications, Installation Tool: Ratchet: Y1MRTC, HYTOOL: Type AH, Aircraft, Cable - MY28 Tool, All Others: MY29-3, MY29-11 Tool, 1 Crimp, Tools, Die Nest Catalog Number, Die Indentor Catalog Number: HYPRESS: H35, Y35BH, Y39, Y39BH Tool, UV2L Die Nest, Y34PLA Die Indentor, Y35P3 Indentor Adaptor, Conductor Type: Commercial/Aircraft Stranded Copper, Package: Box, Wire Strip Length: 5/8 IN, Insulation Support: No

## Product Details

### General

Application	For Aircraft, Light Duty Industrial And General Purpose Applications
Connector Type	Splice
Die Index	41
Feature - Barrel Style	Chamfered
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	Splice
UPC	781810534809

### Dimensions

Dimension - B Length fraction	5/8 in
Dimension - B Length inch	0.62 in
Dimension - L Length Overall mm	36 mm
Dimension - Length Overall inch	1.41 in
Dimension - Outside Diameter inch	0.46 in
Dimension - Strip Length inch	5/8 in

### Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

### Conductor Related

Conductor - Copper Solid Size	2 AWG
Conductor - Copper Str Aircraft Size	AN 2
Conductor - Copper Str Size	2 AWG

Conductor Type	<ul style="list-style-type: none"> <li>• CU C Str-Size</li> <li>• CU C Solid-Size</li> <li>• CU C Str Aircraft-Size</li> </ul>
----------------	--

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)