

YSV4CFXB

by Burndy
Catalog ID: YSV4CFXB

Prop 65 Notice

Compression Splice, 4 AWG, 600 - 35000 V, 2.62 IN L, Die Index: 8.

Features: Long Barrel Length: High Voltage Terminations, Four (4) Center Conductor Stops: Provides A Center Wire Stop For Proper Conductor Insertion, High Pull Out Force: Provides Added Security For Greater Mechanical And Electrical Properties, Belled Cable Entry: A Funnel Type Entry Provide Easy Insertion Of Extra Flexible Cables Plus Offers Mechanical Strain Relief For Individual Strands, Color Code: Gray, Dieless Tools (number Of Crimps): Y81KFT, Y81KFTMBH, PAT81KFT-18V Tool, (1), Tapered End: No, Oil Stop: No, Die Index: 8 Element A, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: Y1MR, Y2MR Tool, (4), Y1MRTC Tool, Y35, Y39, Y750 Tool, U4CRT Die, (2), Y46 Tool, U4CRT Die With PUADP-1 Adapter, (2), Wire Strip Length: 1-5/16 IN, Conductor Type: Flexible Copper



Product Details

General

Application	For Higher voltage applications
Color Code	Gray
Connector Type	Splice
Die Index	8
Feature - Barrel Style	Belled
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	Splice
UPC	781810041499

Dimensions

Dimension - B Length fraction	1-3/16 in
Dimension - B Length inch	1.22 in
Dimension - D inch	0.44 in
Dimension - L Length Overall mm	67 mm
Dimension - Length Overall inch	2.62 in
Dimension - Outside Diameter inch	0.38 in
Dimension - Strip Length inch	1-5/16 in

Conductor Related

Conductor - Copper DLO Size	4 (105/#24) DLO
Conductor - Copper Flex G Size	4 AWG
Conductor - Copper Flex H Size	4 AWG

Conductor - Copper Flex I Size	4 AWG
Conductor - Copper Flex K Size	4 AWG
Conductor - Copper Flex M Size	4 AWG
Conductor - Copper Solid Size	4 AWG
Conductor - Copper Str Compact Size	4
Conductor - Copper Str Compact Size Range	4
Conductor - Copper Str Navy Size	40 (19)
Conductor - Copper Str Size	4 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	100 EA
Minimum Pack Quantity	50

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)