



YSV6CFXBNK

by Burndy
Catalog ID: YSV6CFXBNK

Prop 65 Notice

Nickel Plated Cu Compression Belled End Splice, #6 STR AWG, 600 V to 35 KV, Long Barrel, Blue, 7 Index

Product Details

General

Color Code	Blue
Connector Type	Splice
Die Index	7
Feature - Barrel Style	Belled
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Nickel
Trade Name	HYLINK™
Type	Splice
UPC	781810195949

Dimensions

Dimension - B Length fraction	1-3/16 in
Dimension - B Length inch	1.22 in
Dimension - D inch	0.37 in
Dimension - L Length Overall mm	67 mm
Dimension - Length Overall inch	2.62 in
Dimension - Outside Diameter inch	0.31 in
Dimension - Strip Length inch	1-5/16 in

Conductor Related

Conductor - Copper DLO Size	6 (61/#24) DLO
Conductor - Copper Flex G Size	6 AWG
Conductor - Copper Flex H Size	6 AWG
Conductor - Copper Flex I Size	6 AWG
Conductor - Copper Flex K Size	6 AWG
Conductor - Copper Flex M Size	6 AWG
Conductor - Copper Solid Size	6 AWG
Conductor - Copper Str Compact Size	6
Conductor - Copper Str Navy Size	30 (19)

Conductor - Copper Str Size	6 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	50
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)