

YTA321R2N

by Burndy
Catalog ID: YTA321R2N

Prop 65 Notice

AL primary T-tap connector with slotted tap pad designed for easy disconnecting of tap conductor, For use with Types YKA-R-2N and YKA-A-2N, Barrell Length: 4.97 IN H.

Features: Aluminum Primary T-Tap Connector With Slotted Tap Pad Designed For Easy Disconnecting Of Tap Conductor, Tap Pad Accommodates Compression Terminals Types YKA-R-2N And YKA-A-2N, And Has Positioning Socket For Proper Alignment, On Sizes Larger Than 336.4 KCMIL ACSR, The YTA-R-2N Run Element Has Twopiece Interlocking-Key With Lifting Eye That Simplifies Hotline Installations, Catalog Number Does Not Include Mating Terminal, Compressed / Compact: No, Bolt Size: 1/2 IN, Conductor Type: ACSR, 6201, 5005, Aluminum, Copper, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y750 Tool, U-M Die, (3), U317 Die, (4), Die Index: 317 Element A, Shape: T



Product Details

General

Application	For Copper, Aluminum, ACSR, 6201, 5005, Compressed And Compact Conductors
Connector Type	Tap
Die Index	M
Material	Aluminum
Physical Attribute - Pad Configuration	2 Hole NEMA
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Sub Brand	HYSPLICE
Type	YTA Series
UPC	781810014028
UPC 12 Digit	7818100140288

Dimensions

Dimension - B Length inch	2.62 in
Dimension - Bolt Size fraction	1/2
Dimension - Height inch	4.97 in
Dimension - L Length Overall mm	239 mm
Dimension - Length Overall inch	9.42 in

Conductor Related

Conductor - ACSR Str Size	266.8 (26/7) Partridge kcmil;300.0 (26/7) Ostrich kcmil;336.4 (18/1) Merlin kcmil
Conductor - ACSR Str Size Range	266.8 (26/7) Partridge kcmil-336.4 (18/1) Merlin kcmil
Conductor - AL Str Size	336 kcmil;350 kcmil

Conductor - AL Str Size Range	336 kcmil-350 kcmil
Conductor - Copper Str Size	350 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)