

# YTA33R2N

by Burndy  
Catalog ID: YTA33R2N

Prop 65 Notice

AL primary T-tap connector with slotted tap pad designed for easy disconnecting of tap conductor, For use with Types YKA-R-2N and YKA-A-2N, barrel Length: 2.62 IN L

Features: Aluminum Primary T-Tap Connector With Slotted Tap Pad Designed For Easy Disconnecting Of Tap Conductor, Tap Pad Accommodates Compression Terminals Types YKA-R-2N And YKA-A-2N, And Has Positioning Socket For Proper Alignment, On Sizes Larger Than 336.4 KCMIL ACSR, The YTA-R-2N Run Element Has Twopiece Interlocking-Key With Lifting Eye That Simplifies Hotline Installations, Catalog Number Does Not Include Mating Terminal, Bolt Size: 1/2 IN, Compressed / Compact: No, Conductor Type: ACSR, 6201, 5005, Aluminum, Copper, Die Index: 317 Element A, Shape: T, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y750 Tool, U-M Die, (3), U317 Die, (4)



## Product Details

### General

Application	For Copper, Aluminum, ACSR, 6201, 5005, Compressed And Compact Conductors
Connector Type	Tap
Construction Material - Main	Aluminum
Die Index	M
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Sub Brand	HYSPLICE
Type	YTA-R-2N, Disconnectable
UPC	781810013984
UPC 12 Digit	7818100139844

### Dimensions

Dimension - B Length inch	2.62 in
Dimension - Bolt Size fraction	1/2
Dimension - Height inch	4.97 in
Dimension - L Length Overall mm	239 mm
Dimension - Length Overall inch	9.42 in

### Conductor Related

Conductor - ACSR Str Size	336.4 (26/7) Linnet kcmil;336.4 (30/7) Oriole kcmil;397.5 (18/1) Chickadee kcmil
Conductor - ACSR Str Size Range	336.4 (26/7) Linnet kcmil-397.5 (18/1) Chickadee kcmil
Conductor - AL Str Size	397 kcmil;400 kcmil
Conductor - AL Str Size Range	397 kcmil-400 kcmil

Conductor - Copper Str Size	400 kcmil
-----------------------------	-----------

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)