

YTS32R

by Burndy
Catalog ID: YTS32R

Prop 65 Notice

Aluminum outer sleeve for full tension splice kit, 336.4 Kcmil, 717 Index,
Outer sleeve for Hysplices provides gradual transition of stress



Product Details

General

Connector Type	Splice
Die Index	717
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810000526
UPC 12 Digit	7818100005266

Dimensions

Dimension - L Length Overall mm	439.4
Dimension - Length Overall inch	17.30

Conductor Related

Conductor - ACSR Str Size	336.4 (24/7) Widgeon Kcmil; 336.4 (26/7) Linnet Kcmil; 336.4 (30/7) Oriole Kcmil
Conductor - AL Str Size	336 kcmil
Conductor - AL Str Size Range	336 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)