

YTS351AT

by Burndy
Catalog ID: YTS351AT

Prop 65 Notice

Full Tension Splice for Stranded Aluminum Transmission Line



Product Details

General

Connector Type	Splice
Die Index	720
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810515457
UPC 12 Digit	7818105154577

Dimensions

Dimension - B Length fraction	5-13/16 in
Dimension - B Length inch	5.82 in
Dimension - L Length Overall mm	302 mm
Dimension - Length Overall inch	11.88 in
Dimension - Outside Diameter inch	1.41 in

Conductor Related

Conductor - AL Str Size	500 (37) Hyacinth Kcmil; 556.5 (19) Dahlia Kcmil; 556.5 (37) Mistletoe Kcmil
-------------------------	--

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)