

YTS36R36RSHT

by Burndy
Catalog ID: YTS36R36RSHT

Prop 65 Notice

Compression High Temperature Splice



Product Details

General

Connector Type	Deadend
Die Index	720
Material	Aluminum
UPC	781810484081
UPC 12 Digit	7818104840811

Dimensions

Dimension - B Length inch	12.93 in
Dimension - L Length Overall mm	664 mm
Dimension - Length Overall inch	26.16 in
Dimension - Outside Diameter inch	1.41 in

Conductor Related

Conductor - ACSS Str Size	477 (24/7) kcmil;477 (26/7) kcmil
Conductor - ACSS Str Size Range	477 (24/7) kcmil-477 (26/7) kcmil

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)