

YTS391AT

by Burndy
Catalog ID: YTS391AT

Prop 65 Notice

Al Tube Full Tension Splice, EHV, 795 - 800 kcmil Al, 16.36" L, 724 Index



Product Details

General

Connector Type	Splice
Die Index	724
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810016244
UPC 12 Digit	7818100162444

Dimensions

Dimension - L Length Overall mm	416 mm
Dimension - Length Overall inch	16.36 in
Dimension - Outside Diameter inch	1.61

Conductor Related

Conductor - AL Str Size	795 kcmil;800 kcmil
Conductor - AL Str Size Range	795 kcmil-800 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)