



## YTS391A

by Burndy  
Catalog ID: YTS391A

Prop 65 Notice

Al Tube Full Tension Splice, 795 kcmil Al, 37 Str, 795 kcmil Al, 61 Str, 800 kcmil Al, 61 Str, 15.81" L, For Stranded Al Cable

## Product Details

### General

Connector Type	Splice
Die Index	724
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810016220
UPC 12 Digit	7818100162200

### Dimensions

Dimension - L Length Overall mm	402 mm
Dimension - Length Overall inch	15.81 in

### Conductor Related

Conductor - AL Str Size	795 (37, 61) Kcmil; 800 (61) Kcmil
-------------------------	------------------------------------

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)