

YTS39A

by Burndy
Catalog ID: YTS39A

Prop 65 Notice

Al Tube Full Tension Splice, 715.5, 750 kcmil Al, 230 kV, 13.36" L, 724 Index



Product Details

General

Connector Type	Splice
Die Index	724
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810016169
UPC 12 Digit	7818100161699

Dimensions

Dimension - L Length Overall mm	339 mm
Dimension - Length Overall inch	13.36 in

Conductor Related

Conductor - AL Str Size	715.5 (37, 61) Kcmil; 750 (61) Kcmil
-------------------------	--------------------------------------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)