

# YTS451R48RS

by Burndy  
Catalog ID: YTS451R48RS

Prop 65 Notice

Full Tension Splice Kit for ACSR Conductor



## Product Details

### General

Connector Type	Splice
Trade Name	HYSPLICE™
UPC	781810507018
UPC 12 Digit	7818105070188

### Dimensions

Dimension - Length Overall inch	28.96 in
Dimension - Outside Diameter inch	1.80 in

### Conductor Related

Conductor - ACSR Str Size	715.5 (26/7) Starling kcmil;715.5 (30/19) Redwing kcmil;795 (54/7) Condor kcmil;795 (26/7) Drake kcmil
Conductor - ACSR Str Size Range	715.5 (26/7) Starling kcmil-795 (26/7) Drake kcmil

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	No

### Logistics

Minimum Pack Quantity	6
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)