

YTS48AT

by Burndy
Catalog ID: YTS48AT

Prop 65 Notice

Al Full Tension Splice For Stranded Aluminum Transmission Line, 2000 kcmil, 345 kV, 735 Index, Extra High Voltage Applications



Product Details

General

Connector Type	Splice
Die Index	735
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810183106
UPC 12 Digit	7818101831066

Dimensions

Dimension - L Length Overall mm	585 mm
Dimension - Length Overall inch	23.02 in

Conductor Related

Conductor - AL Str Size	2000 kcmil
-------------------------	------------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)