



YTS49R483RS

by Burndy
Catalog ID: YTS49R483RS

Prop 65 Notice

Two piece full tension splice kit, 1113Kcmil, 727 Index, Kit includes both Steel and aluminum sleeves

Product Details

General

Connector Type	Splice
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810479223
UPC 12 Digit	7818104792233

Dimensions

Dimension - B Length inch	4.01 in
Dimension - L Length Overall mm	737 mm
Dimension - Length Overall inch	29.02 in
Dimension - Outside Diameter inch	1.97 in

Conductor Related

Conductor - ACSR Str Size	1033.5 (45/7) Ortolan kcmil;1113 (45/7) Bluejay kcmil
Conductor - ACSR Str Size Range	1033.5 (45/7) Ortolan kcmil-1113 (45/7) Bluejay kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	6
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)