

YTS49RT48RSHT

by Burndy
Catalog ID: YTS49RT48RSHT

Prop 65 Notice

Full Tension ACSS EHV Splice Kits, YTS49RTH Aluminium Sleeve (Qty. 1), YTS48RS Steel Sleeve (Qty. 1), CURLEW 1033.5 (54/7) kcmil



Product Details

General

Application	For ACSS Conductor, Corona free operation up to 550 KV
Connector Type	Splice
Die Index	727;726
Die Type	L727 for Aluminium Sleeve, L726 Steel Sleeve
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810501368
UPC 12 Digit	7818105013688

Dimensions

Dimension - B Length inch	4.00 in
Dimension - Length Overall inch	37.02 in
Dimension - Outside Diameter inch	1.97 in

Electrical Ratings

Voltage - Maximum	550 kV
-------------------	--------

Conductor Related

Conductor - ACSS Str Size	CURLEW 1033.5 (54/7) kcmil
Conductor - Material	Aluminum

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed	No
-----------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)