

# YTS49RT48RS

by Burndy  
Catalog ID: YTS49RT48RS

Prop 65 Notice

Full Tension Splice Kit for ACSR Conductor EHV



## Product Details

### General

Connector Type	Splice
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810515747
UPC 12 Digit	7818105157477

### Dimensions

Dimension - B Length fraction	4 in
Dimension - L Length Overall mm	737 mm
Dimension - Length Overall inch	29.02 in
Dimension - Outside Diameter inch	1.97 in

### Conductor Related

Conductor - ACSR Str Size	1033.5 (54/7) Curlew kcmil
---------------------------	----------------------------

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)