

YTS49R

by Burndy
Catalog ID: YTS49R

Prop 65 Notice

Aluminum Sleeve, 1033.5 - 1113 Kcmil ACSR, 230 V, 29.02" L, 727 Index,
Included in Full Tension Splice



Product Details

General

Connector Type	Splice
Die Index	727
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810016114
UPC 12 Digit	7818100161144

Dimensions

Dimension - L Length Overall mm	737.1 mm
Dimension - Length Overall inch	29.02 in

Conductor Related

Conductor - ACSR Str Size	1033.5 (45/7) Ortolan Kcmil; 1033.5 (54/7) Curlew Kcmil; 1113 (45/7) Bluejay Kcmil
---------------------------	--

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)