

YTS52RT59RSHT

by Burndy
Catalog ID: YTS52RT59RSHT

Prop 65 Notice

Full Tension ACSS EHV Splice Kits, YTS52RHT Aluminium Sleeve (Qty. 1), YTS59RS Steel Sleeve (Qty. 1), 1272 (54/19) kcmil-1351.5 (54/19) kcmil



Product Details

General

Application	For ACSS Conductor, Corona free operation up to 550 KV
Connector Type	Splice
Die Index	728;726
Die Type	L728 for Aluminium Sleeve, L726 Steel Sleeve
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810515815
UPC 12 Digit	7818105158155

Dimensions

Dimension - B Length inch	4.07 in
Dimension - Length Overall inch	50.33 in
Dimension - Outside Diameter inch	2.25 in

Electrical Ratings

Voltage - Maximum	550 kV
-------------------	--------

Conductor Related

Conductor - ACSS Str Size	1272 (54/19) kcmil;1351.5 (42/7) kcmil;1351.5 (45/7) kcmil;1351.5 (48/7) kcmil;1351.5 (54/19) kcmil
Conductor - ACSS Str Size Range	1272 (54/19) kcmil-1351.5 (54/19) kcmil
Conductor - Material	Aluminum

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)