

YTS592AR

by Burndy
Catalog ID: YTS592AR

Aluminum Tube Full Tension HYSPLICE™ for ACAR, 2493 Kcmil



Product Details

General

Connector Type	Splice
Material	Aluminum
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810324721
UPC 12 Digit	7818103247211

Dimensions

Dimension - L Length Overall mm	720 mm
Dimension - Length Overall inch	28.34 in

Conductor Related

Conductor - ACAR Str Size	2493 (54-37) Kcmil
---------------------------	--------------------

Certifications and Compliance

Standards - RoHS Compliance Status	UI
------------------------------------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)