

YTS59RT59RSHT

by Burndy
Catalog ID: YTS59RT59RSHT

Full Tension ACSS EHV Splice Kits, YTS59RTHT Aluminium Sleeve (Qty. 1), YTS59RS Steel Sleeve (Qty. 1), BLUEBIRD 2156 (84/19) kcmil



Product Details

General

| | |
|----------------|--|
| Application | For ACSS Conductor, Corona free operation up to 550 kV |
| Connector Type | Splice |
| Die Index | 735;726 |
| Die Type | L735 for Aluminium Sleeve, L726 Steel Sleeve |
| Material | Aluminum |
| Trade Name | HYSPLICE™ |
| UPC | 781810516034 |
| UPC 12 Digit | 7818105160344 |

Dimensions

| | |
|-----------------------------------|----------|
| Dimension - B Length inch | 4.07 in |
| Dimension - Length Overall inch | 50.91 in |
| Dimension - Outside Diameter inch | 2.50 in |

Electrical Ratings

| | |
|-------------------|--------|
| Voltage - Maximum | 550 kV |
|-------------------|--------|

Conductor Related

| | |
|---------------------------|-----------------------------|
| Conductor - ACSS Str Size | BLUEBIRD 2156 (84/19) kcmil |
| Conductor - Material | Aluminum |

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Standards - RoHS Compliance Status | UI |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)