



YTU25R2R

by Burndy
Catalog ID: YTU25R2R

Prop 65 Notice

Al Compression T-Tap Connector, 1/0 AWG ACSR/Al/Cu(Run), #2 Str ACSR/Al/Cu(Tap)

Product Details

General

| | |
|---------------------------|----------------|
| Connector Type | Tap |
| Material | Aluminum Alloy |
| Plated | N |
| Plating Type | Unplated |
| Prefilled Oxide Inhibitor | Y |
| UPC | 781810124642 |
| UPC 12 Digit | 7818101246422 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - B Length inch | 0.82 in |
| Dimension - Height inch | 2.40 in |
| Dimension - L Length Overall mm | 123 mm |
| Dimension - Length Overall inch | 4.84 in |

Conductor Related

| | |
|----------------------------|--------------------|
| Conductor - ACSR Str Run | 1/0 AWG |
| Conductor - ACSR Str Tap | 2 AWG(6-1,7-1 STR) |
| Conductor - AL Str Run | 1/0 AWG |
| Conductor - AL Str Tap | 2 AWG STR |
| Conductor - Copper Str Run | 80 kcmil |
| Conductor - Copper Str Tap | 2 AWG(7,8 STR) |

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 6 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)