

YTU30R30R

by Burndy
Catalog ID: YTU30R30R

Prop 65 Notice

Al Compression T-Tap Connector, 266.8 kcmil ACSR, 300 - 250 kcmil Cu/Al (Run & Tap)



Product Details

General

| | |
|---------------------------|----------------|
| Connector Type | Tap |
| Die Index Run Side | M |
| Die Index Tap Side | M |
| Material | Aluminum Alloy |
| Plated | N |
| Plating Type | Unplated |
| Prefilled Oxide Inhibitor | Y |
| UPC | 781810155608 |
| UPC 12 Digit | 7818101556088 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - B Length inch | 2.67 in |
| Dimension - Height inch | 4.32 in |
| Dimension - L Length Overall mm | 222 mm |
| Dimension - Length Overall inch | 8.75 in |

Conductor Related

| | |
|----------------------------------|--|
| Conductor - ACSR Str Run | 266.8 (18/1) Waxwing kcmil;266.8 (26/7) Owl kcmil;266.8 (26/7) Partridge kcmil |
| Conductor - ACSR Str Run Range | 266.8 (18/1) Waxwing kcmil-266.8 (26/7) Partridge kcmil |
| Conductor - ACSR Str Tap | 266.8 (18/1) Waxwing kcmil;266.8 (26/7) Owl kcmil |
| Conductor - ACSR Str Tap Range | 266.8 (18/1) Waxwing kcmil-266.8 (26/7) Owl kcmil |
| Conductor - AL Str Run | 266 kcmil;300 kcmil |
| Conductor - AL Str Run Range | 266 kcmil-300 kcmil |
| Conductor - AL Str Tap | 266 kcmil;300 kcmil |
| Conductor - AL Str Tap Range | 266 kcmil-300 kcmil |
| Conductor - Copper Str Run | 250 kcmil;300 kcmil |
| Conductor - Copper Str Run Range | 250 kcmil-300 kcmil |
| Conductor - Copper Str Tap | 250 kcmil(12,19,37 STR), 300 kcmil(19,37 STR) |
| Conductor - Copper Str Tap Range | 250 kcmil(12,19,37 STR)-300 kcmil(19,37 STR) |

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)