



YTU321R25R

by Burndy
Catalog ID: YTU321R25R

Prop 65 Notice

Al Compression T-Tap Connector, 300 - 336.4 kcmil ACSR,6201,5005, 350 - 336.4 kcmil Al, 350 kcmil Cu(Run), 1/0 AWG ACSR/Al/Cu(Tap)

Product Details

General

Connector Type	Tap
Material	Aluminum Alloy
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
UPC	781810298404
UPC 12 Digit	7818102984044

Dimensions

Dimension - B Length inch	2.09 in
Dimension - Height inch	3.81 in
Dimension - L Length Overall mm	180 mm
Dimension - Length Overall inch	7.09 in

Conductor Related

Conductor - ACSR Str Run	336.4 kcmil, 300 kcmil
Conductor - ACSR Str Run Range	300 kcmil-336.4 kcmil
Conductor - ACSR Str Tap	1/0 AWG(6-1 STR)
Conductor - AL Str Run	350 kcmil, 336.4 kcmil
Conductor - AL Str Run Range	336.4 kcmil-350 kcmil
Conductor - AL Str Tap	1/0 AWG(7,19 STR)
Conductor - Copper Str Run	350 kcmil
Conductor - Copper Str Tap	1/0 AWG(7,19,12 STR)

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)