

# YTU321R2R

by Burndy  
Catalog ID: YTU321R2R

Prop 65 Notice

Al Compression T-Tap Connector, 300 - 336.4 kcmil ACSR, 350 - 336.4 kcmil Al, 350 kcmil Cu(Run), #2 AWG ACSR/Al/Cu(Tap)



## Product Details

### General

Die Index Run Side	M;705
Die Index Tap Side	BG
Material	Aluminum Alloy
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
UPC	781810000397
UPC 12 Digit	7818100003977

### Dimensions

Dimension - B Length inch	2.09 in
Dimension - Height fraction	2-5/8 in
Dimension - Height inch	3.81 in
Dimension - L Length Overall mm	180 mm
Dimension - Length Overall inch	7.09 in

### Conductor Related

Conductor - ACSR Str Run	300.0 (26/7) Ostrich kcmil;336.4 (18/1) Merlin kcmil
Conductor - ACSR Str Run Range	300.0 (26/7) Ostrich kcmil-336.4 (18/1) Merlin kcmil
Conductor - ACSR Str Tap	2 (6/1) Sparrow AWG;2 (7/1) Sparate AWG
Conductor - ACSR Str Tap Range	2 (6/1) Sparrow AWG-2 (7/1) Sparate AWG
Conductor - AL Str Run	336 kcmil;350 kcmil
Conductor - AL Str Run Range	336 kcmil-350 kcmil
Conductor - AL Str Tap	2 AWG
Conductor - Copper Str Run	350 kcmil
Conductor - Copper Str Tap	2 AWG

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)