

YTU321R30R

by Burndy
Catalog ID: YTU321R30R

Al Compression T-Tap Connector, 300-336.4 kcmil ACSR, 350-336.4 kcmil Al, 350 kcmil Cu(Run), 266.8 kcmil ACSR, 300, 266.8, 250 kcmil Al, 300-250 kcmil Cu(Tap)



Product Details

General

Connector Type	Tap
Material	Aluminum Alloy
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
UPC	781810324752
UPC 12 Digit	7818103247522

Dimensions

Dimension - B Length inch	2.71 in
Dimension - Height inch	4.36 in
Dimension - L Length Overall mm	222 mm
Dimension - Length Overall inch	8.75 in

Conductor Related

Conductor - ACSR Str Run	336.4 kcmil, 300 kcmil
Conductor - ACSR Str Run Range	300 kcmil-336.4 kcmil
Conductor - ACSR Str Tap	266.8 kcmil(18-1,6-7,26-7 STR)
Conductor - AL Str Run	350 kcmil, 336.4 kcmil
Conductor - AL Str Run Range	336.4 kcmil-350 kcmil
Conductor - AL Str Tap	300 kcmil(19,37 STR), 266.8 kcmil(7,19,37,STR),250 kcmil(19,37 STR)
Conductor - AL Str Tap Range	250kcmil(19,37 STR)-300 kcmil(19,37 STR)
Conductor - Copper Str Run	350 kcmil
Conductor - Copper Str Tap	250 kcmil(12,19,37 STR), 300 kcmil(19,37 STR)
Conductor - Copper Str Tap Range	250 kcmil(12,19,37 STR)-300 kcmil(19,37 STR)

Certifications and Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)