

YTU33R33R

by Burndy
Catalog ID: YTU33R33R

Prop 65 Notice

1-piece heavy wall AL compression tap connector for secondary service drop and transformer tap to primary or secondary, 8-3/4 IN L



Product Details

General

Connector Type	Tap
Die Index Run Side	M
Die Index Tap Side	M
Material	Aluminum Alloy
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
UPC	781810156001
UPC 12 Digit	7818101560011

Dimensions

Dimension - B Length inch	2.67 in
Dimension - Height fraction	4-1/3 in
Dimension - Height inch	4.32 in
Dimension - L Length Overall mm	222 mm
Dimension - Length Overall inch	8.75 in

Conductor Related

Conductor - ACSR Str Run	336.4 (30/7) Oriole kcmil;397.5 (18/1) Chickadee kcmil
Conductor - ACSR Str Run Range	336.4 (30/7) Oriole kcmil-397.5 (18/1) Chickadee kcmil
Conductor - ACSR Str Tap	336.4 (30/7) Oriole kcmil;397.5 (18/1) Chickadee kcmil
Conductor - ACSR Str Tap Range	336.4 (30/7) Oriole kcmil-397.5 (18/1) Chickadee kcmil
Conductor - AL Str Run	397 kcmil;400 kcmil
Conductor - AL Str Run Range	397 kcmil-400 kcmil
Conductor - AL Str Tap	397 kcmil;400 kcmil
Conductor - AL Str Tap Range	397 kcmil-400 kcmil
Conductor - Copper Str Run	400 kcmil
Conductor - Copper Str Tap	400 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	6
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)