

# YTW36R36REKHT

by Burndy  
Catalog ID: YTW36R36REKHT

Prop 65 Notice

Single Pad Full Tension Compression Deadend for ACSS Conductor



## Product Details

### General

Connector Type	Deadend
Die Index	720
Material	Aluminum
Material - Clevis	Steel
Physical Attribute - Pad Orientation	15 Degree Angle
Prefilled Oxide Inhibitor	N
UPC	781810484074
UPC 12 Digit	7818104840744

### Dimensions

Dimension - B Length inch	2.50 in
Dimension - Hole Size inch	0.88 in
Dimension - L Length Overall mm	595 mm
Dimension - Length Overall inch	23.41 in
Dimension - Outside Diameter inch	1.41 in
Dimension - Pad Width inch	3.25 in
Dimension - Width inch	0.62 in
Dimension - Width mm	16 mm

### Conductor Related

Conductor - ACSS Str Size	477 (26/7) kcmil
---------------------------	------------------

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	No

### Logistics

Minimum Pack Quantity	50
-----------------------	----

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)