

YTW430MMRC15ACK5LS

by Burndy
Catalog ID: YTW430MMRC15ACK5LS

Prop 65 Notice

Full Tension, BRUSSELS ACCC® Deadend Connector, Accomodates 430 mm²



* Representative image

Product Details

General

Application	For ACCC Conductor, Corona free operation up to 230 KV
Connector Type	Deadend
Prefilled Oxide Inhibitor	N
UPC	781810551936
UPC 12 Digit	7818105519366

Dimensions

Dimension - Inside Diameter inch	1.09 in
Dimension - Length Overall inch	15.5 in
Dimension - Outside Diameter inch	1.32 in
Weight	14 lb

Electrical Ratings

Voltage - Maximum	230 kV
-------------------	--------

Conductor Related

Conductor - ACCC Str Size	BRUSSELS 430mm ²
Conductor - Material	Aluminum

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)