

# YTW48RT48REKHT

by Burndy  
Catalog ID: YTW48RT48REKHT

Prop 65 Notice

Full Tension, ACSS EHV Deadend Kits, Hardware TMH24, CARDINAL 954 (54/7) kcmil, YTW48RT48REKHTNT Aluminum Dead End Assy., BYNA49RT15HHT Terminal



## Product Details

### General

Application	For ACSS Conductor, Corona free operation up to 230 KV
Connector Type	Deadend
Physical Attribute - Number of Holes	4
Prefilled Oxide Inhibitor	N
UPC	781810493663
UPC 12 Digit	7818104936633

### Dimensions

Dimension - B Length inch	2.69 in
Dimension - Hole Size inch	1.25 in
Dimension - Length Overall inch	29.50 in
Dimension - Pad Width inch	3.25 in
Dimension - Width inch	0.75 in

### Electrical Ratings

Voltage - Maximum	230 kV
-------------------	--------

### Conductor Related

Conductor - ACSS Str Size	CARDINAL 954 (54/7) kcmil
Conductor - ACSS Str Size Range	954 (54/7) kcmil
Conductor - Material	Aluminum

### Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

### Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)