

YTW52RT50REKHTSC

by Burndy
Catalog ID: YTW52RT50REKHTSC

Full Tension, ACSS EHV Deadend Kits, Hardware TMH22, FINCH 1113 (54/19) kcmil, YTW52RT50REKHTNT Aluminum Dead End Assy., BYNA52RT15HT Terminal, STS44A4NCG2 (Qty.2)



* Representative image

Product Details

General

Connector Type	Deadend
Physical Attribute - Number of Holes	4
Prefilled Oxide Inhibitor	N
UPC	781810497418
UPC 12 Digit	7818104974188

Electrical Ratings

Voltage - Maximum	230 kV
-------------------	--------

Conductor Related

Conductor - ACSS Str Size	FINCH 1113 (54/19) kcmil
Conductor - Material	Aluminum

Certifications and Compliance

Standards - RoHS Compliance Status	UI
------------------------------------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)