

YTW52RT50REKHT

by Burndy
Catalog ID: YTW52RT50REKHT

Prop 65 Notice

Full Tension, ACSS EHV Deadend Kits, Hardware TMH9, FINCH 1113 (54/19) kcmil, YTW52RT50REKHTNT Aluminum Dead End Assy., BYNA52RT15HHT Terminal



Product Details

General

Application	For ACSS Conductor, Corona free operation up to 230 KV
Connector Type	Deadend
Physical Attribute - Number of Holes	4
Prefilled Oxide Inhibitor	N
UPC	781810496312
UPC 12 Digit	7818104963122

Dimensions

Dimension - B Length inch	2.69 in
Dimension - Hole Size inch	1.25 in
Dimension - Length Overall inch	35.55 in
Dimension - Pad Width inch	3.25 in
Dimension - Width inch	1.00 in

Electrical Ratings

Voltage - Maximum	230 kV
-------------------	--------

Conductor Related

Conductor - ACSS Str Size	FINCH 1113 (54/19) kcmil
Conductor - ACSS Str Size Range	1113 (54/19) kcmil
Conductor - Material	Aluminum

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)