

YTW56RT590REKHT

by Burndy
Catalog ID: YTW56RT590REKHT

Prop 65 Notice

Full Tension, ACSS EHV Deadend Kits, Hardware TMH9, FALCON 1590 (54/19) kcmil, YTW56RT590REKHTNT Aluminum Dead End Assy., BYNA56RT15HHT Terminal



Product Details

General

Application	For ACSS Conductor, Corona free operation up to 230 KV
Connector Type	Deadend
Physical Attribute - Number of Holes	4
Prefilled Oxide Inhibitor	N
UPC	781810490914
UPC 12 Digit	7818104909144

Dimensions

Dimension - B Length inch	2.69 in
Dimension - Hole Size inch	1.25 in
Dimension - Length Overall inch	35.99 in
Dimension - Pad Width inch	4.00 in
Dimension - Width inch	1.00 in

Electrical Ratings

Voltage - Maximum	230 kV
-------------------	--------

Conductor Related

Conductor - ACSS Str Size	FALCON 1590 (54/19) kcmil
Conductor - ACSS Str Size Range	1590 (54/19) kcmil
Conductor - Material	Aluminum

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)