

# YTW56RT590REK

by Burndy  
Catalog ID: YTW56RT590REK

Prop 65 Notice

Single Pad, EHV Full Tension Deadend for ACSR Conductor



\* Representative image

## Product Details

### General

Connector Type	Deadend
Die Index	729
Material - Clevis	Steel
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Configuration	NEMA
Physical Attribute - Pad Orientation	15 Degree Angle
UPC	781810489055
UPC 12 Digit	7818104890555

### Dimensions

Dimension - B Length inch	2.69 in
Dimension - Bolt Size fraction	1/2
Dimension - F Width Center to Center inch	1.75 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	813 mm
Dimension - Length Overall inch	31.99 in
Dimension - Pad Width inch	4.00 in

### Conductor Related

Conductor - ACSR Str Size	1590 (54/19) Falcon kcmil
---------------------------	---------------------------

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)