

Z34NRB

by Burndy
Catalog ID: Z34NRB

Prop 65 Notice

Socket & Nut Assembly, 500 kcmil, 7/8" - 14 Stud



Product Details

General

Connector Type	Nut
Installation Torque Recommended in-lb	700 lb-in
Insulation Type	Rubber
Material	Bronze Alloy, Leaded
Plated	Y
Plating Type	Tin - Electro Plated
UPC	781810017470
UPC 12 Digit	7818100174700

Dimensions

Dimension - B Length fraction	11/16 in
Dimension - Cross Flats inch	1.50 in
Dimension - Length Overall inch	1.5
Dimension - Width inch	2.13 in
Weight	0.74 lb

Conductor Related

Conductor - Copper Str Size	500 kcmil
Conductor - Copper Str Size Range	500 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)