

ZM1025B

by Burndy
Catalog ID: ZM1025B

Prop 65 Notice

MOLE ASSY



Product Details

General

Connector Type	Mole
Insulation	Y
Material	Copper
Number Of Outlets	10
Plated	Y
Plating Type	Tin
Trade Name	MOLE™
UPC	781810134528
UPC 12 Digit	7818101345288

Dimensions

Dimension - Cross Flats inch	1.62 in
Dimension - Height inch	4.5
Dimension - Length Overall inch	18.5 in
Dimension - Outside Diameter inch	1.89 in
Dimension - Pad Width inch	4.5 in
Dimension - Width inch	4.5 in

Conductor Related

Conductor - Copper Str Size	2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil;850 kcmil;900 kcmil;1000 kcmil
Conductor - Copper Str Size Range	2 AWG-1000 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity

1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)