



ACC-ECTA1211

by WILEY
Catalog ID: ACC-ECTA1211

Wiley Edge Clip with Cable Tie, Vertical (90 deg.) parallel installation

- Route cable bundles without the need for mounting holes or additional hardware
- Installs in a vertical/parallel (90°) or horizontal/perpendicular (180°) orientation
- Steel lances securely anchor clips to module frames or purlins
- Offered in various nylon types with 50 lb tensile strength: UV resistant, high impact heat stabilized Nylon 6/6 • UV resistant Nylon 12 which provides excellent UV, chemical and moisture resistance

Product Details

General

Application	<ul style="list-style-type: none"> • For routing cable bundles without requiring mounting holes or additional hardware, Available in Nylon 6/6 or Nylon 12 for either horizontal/perpendicular (90°) or vertical/ parallel (180°) styles • 50 lb tensile strength, Steel lances securely anchor clips to module frames / purlins, 3 standard cable tie lengths (8", 11", 14") encompass maximum bundle diameters of 1.95" to 3.94" • Custom lengths available
Material	Nylon 12
Tensile Strength	50 lb
UPC	621945554351

Dimensions

Dimension - Bundle Diameter Max inch	2.95 in
Length	11 in

Logistics

Carton Quantity	1000
-----------------	------

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)